

Dipping Grade Flux Paste



www: im-metalioining.com

Easy-flo™ Low Temperature Grade Flux Paste

Easy-flo™ Low Temperature Grade Flux paste is a brazing flux suitable for use with silver brazing filler metals. It has a working range of 550-750°C and is recommended for use with filler metals melting below 700°C (such as the low melting point Silver-flo™ and Easy-flo™ filler metals). It is highly active very early on in the brazing cycle, exhibits very little bubbling during heating and has a relatively low viscosity when molten. These facts make it suitable for induction brazing or very fast, short heating cycles. Easy-flo™ Low Temperature Grade Flux paste formerly sold as Easy-flo™ Dipping Grade paste.

Easy-flo™ Low Temperature Grade Flux is suitable for use on all the common engineering materials (copper, brass, mild steel and stainless steel), but not aluminium. It performs particularly well on copper and copper alloys. JM special purpose fluxes are required when brazing aluminium bronze, certain grades of stainless steel, tungsten, molybdenum and tungsten carbide or where protracted heating is involved.

Conforms to: EN 1045: FH10 Working range: 550-750°C

Directions for Use

In order to ensure a consistent mixture throughout, stir the flux paste well before use. The flux paste has been formulated to have a thin consistency to allow parts to be fluxed by immersion into the paste. When fluxed in this way, parts achieve a uniform thin covering of flux paste. The flux can be thinned by adding more water and is suitable for automated application in systems using mechanical pumps. Alternatively flux paste should be brushed onto the joint surfaces before assembly. Further flux should then be applied externally either side of the joint mouth.

It is good practice to mechanically clean and degrease the joint surface before applying flux. Heat slowly and evenly to the brazing temperature, without local overheating. Use the flux as a temperature guide - it will become clear or opaque as brazing temperature is approached. If blackening of the flux occurs this is often a sign of insufficient flux, overheating or flux exhaustion.

Flux Residue Removal

The flux residues of this product, left after completion of the brazing operation, are corrosive and should be removed. They can be readily removed by soaking in hot water at a temperature >40°C for between 15 and 30 minutes. Any remaining residues can then be brushed off in running water.

Product Availability

1kg Plastic Pots 7kg Plastic Pots 25kg Plastic Containers

Telephone: +44 (0) 1763 253200

Easy-flo™ and Silver-flo™ are Johnson Matthey trademarks and are registered to JM in the EU and certain other countries.

Johnson Matthey Plc cannot anticipate all conditions under which this information and our products or the products of other manufacturers in combination with our products will be used. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is given in good faith, being based on the latest information available to Johnson Matthey Plc and is, to the best of Johnson Matthey Plc's knowledge and belief, accurate and reliable at the time of preparation. However, no representation, warranty or guarantee is made as to the accuracy or completeness of the information and Johnson Matthey Plc assumes no responsibility therefore and disclaims any liability for any loss, damage or injury howsoever arising (including in respect of any claim brought by any third party) incurred using this information. The product is supplied on the condition that the user accepts responsibility to satisfy himself as to the suitability and completeness of such information for his own particular use. Freedom from patent or any other proprietary rights of any third party must not be assumed. The text and images on this document are Copyright and property of Johnson Matthey.

This datasheet may only be reproduced as information, for use with or for resale of Johnson Matthey products. The JM logo©, Johnson Matthey name© and product names referred to in this document are trademarks of Johnson Matthey. Easy-flo® and Silver-flo® are registered to JM in the EU. Sil-fos™ is registered to JM in the UK and certain other countries but is marketed as Mattiphos™ in Germany and the USA.

JM(X)